



Find the best products in:
maxcadinc.com

ZIRCONIUM Disks and in Block

ZIRCONIUM MAXCAD INC.

Blocks and zirconium discs, in the whole range of shades in vita classic scale.

Colors / Application

VITA CLASSIC scale.
HT / ST / TT

Products

Blocks - Boxes with 6 units.
Disc - Boxes with 1 unit.

High Quality

- Premium Product -
Maxcad Dental Supplies.

Contact

 maxcadinc.com


 info@maxcadinc.com



ZIRCONIUM DISILICATE



Strength (Mpa)



Indications


| Indication | ST White | ST-Color | ST-ML | TT White | TT-Color | TT-ML |
|---|----------|----------|-------|----------|----------|-------|
| Single crown | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ |
| 2-3 unit bridges | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ |
| 3-4 unit bridges (with one pontic) | ✓ | ✓ | ✓ | | | |
| Bridges over 5 units (Less than 3 sequential pontics for the anterior, Less than 2 sequential pontics for the posterior) | ✓* | ✓* | ✓* | | | |
| Cantilever bridges (Except the patient with bruxism) | ✓ | ✓ | ✓ | | | |
| Inlay bridges (Except the patient with bruxism) | ✓ | ✓ | ✓ | | | |
| Maryland bridges (Except the patient with bruxism) | ✓ | ✓ | ✓ | | | |
| Telescopic crowns | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ |
| Veneers | | | | ✓ | ✓ | ✓ |

✓ recommended to make bridge

✓* can be made bridge but not recommended

FEATURES

Indications



How to use the MAX CAD 16 shades Stain Kit:

The MAX CAD 16 shades stains kit is formulated to work with MAX CAD ST pre-shaded zirconia discs. This table shows you how to combine the stains with MAX CAD pre-shaded ST zirconia to achieve the correct end result:

Classical 16 shades A-D combination table

| The shade you want | Use this ST color zirconia | Stain needed | Incisal and fossae stain |
|--------------------|----------------------------|--------------|--|
| A1 | A1 | None needed | <p>Purple/Blue as necessary Brown or red-brown for the fissures</p> <p>Note:</p> <p>ST 6 shades zirconia (A1/A2/A3/B1/B3/C2) + Max Cad 16 shades stains kit = VITA 16 shades restorations</p> |
| A2 | A2 | None needed | |
| A3 | A3 | None needed | |
| A3.5 | A3 | Use A3.5 | |
| A4 | A3 | Use A4 | |
| B1 | B1 | None needed | |
| B2 | B1 | Use B2 | |
| B3 | B3 | None needed | |
| B4 | B3 | Use B4 | |
| C1 | A1 | Use C1 | |
| C2 | C2 | None needed | |
| C3 | C2 | Use C3 | |
| C4 | C2 | Use C4 | |
| D2 | A1 | Use D2 | |
| D3 | A2 | Use D3 | |
| D4 | C2 | Use D4 | |





MAX CAD zirconia shade guide



SPECIFICATION



SPECIFICATION

| Applied for | Specification(mm) | Package | HT white | ST white | ST color | ST Multi-layer | TT white | TT color | TT Multi-layer |
|--|--------------------------|-----------|----------|----------|----------|----------------|----------|----------|----------------|
| Open CAD/CAM System  | D98x10 (stepless) | 1pc/box | √ | √ | √ | | √ | √ | |
| | D98x12 (step & stepless) | 1pc/box | √ | √ | √ | √ | √ | √ | √ |
| | D98x14 (step & stepless) | 1pc/box | √ | √ | √ | √ | √ | √ | √ |
| | D98x16 (step & stepless) | 1pc/box | √ | √ | √ | √ | √ | √ | √ |
| | D98x18 (step & stepless) | 1pc/box | √ | √ | √ | √ | √ | √ | √ |
| | D98x20 (step & stepless) | 1pc/box | √ | √ | √ | √ | √ | √ | √ |
| | D98x22 (step & stepless) | 1pc/box | √ | √ | √ | | √ | √ | |
| Cerec in lab (Sirona) System  | 20x14x15 | 12pcs/box | √ | √ | √ | | √ | | |
| | 20x19x15 | 10pcs/box | √ | √ | √ | | √ | | |
| | 40x14x15 | 8pcs/box | √ | √ | √ | | √ | | |
| | 40x19x15 | 6pcs/box | √ | √ | √ | | √ | | |
| | 55x19x15 | 5pcs/box | √ | √ | √ | | √ | | |
| | 65x25x22 | 4pcs/box | √ | √ | √ | | √ | | |
| | 65x40x22 | 2pcs/box | √ | √ | √ | | √ | | |
| Zirkonzahn CAD/CAM System  | D95x10 | 1pc/box | √ | √ | √ | | √ | | |
| | D95x12 | 1pc/box | √ | √ | √ | | √ | | |
| | D95x14 | 1pc/box | √ | √ | √ | | √ | | |
| | D95x16 | 1pc/box | √ | √ | √ | | √ | | |
| | D95x18 | 1pc/box | √ | √ | √ | | √ | | |
| | D95x20 | 1pc/box | √ | √ | √ | | √ | | |
| | D95x22 | 1pc/box | √ | √ | √ | | √ | | |
| Amann Girrbach CAD/CAM System  | 89x71x10 | 1pcs/box | √ | √ | √ | | √ | | |
| | 89x71x12 | 1pcs/box | √ | √ | √ | | √ | | |
| | 89x71x14 | 1pcs/box | √ | √ | √ | | √ | | |
| | 89x71x16 | 1pcs/box | √ | √ | √ | | √ | | |
| | 89x71x18 | 1pcs/box | √ | √ | √ | | √ | | |
| | 89x71x20 | 1pcs/box | √ | √ | √ | | √ | | |
| | 89x71x22 | 1pcs/box | √ | √ | √ | | √ | | |
| 89x71x25 | 1pcs/box | √ | √ | √ | | √ | | | |

SPECIFICATION



Contact

 maxcadinc.com

 info@maxcadinc.com

